

Product data sheet

Specifications



Push-to-test pilot light head,
Harmony 9001SK, plastic, without
cap, 30mm, LED green, 120V

9001SKT38LG

Main

Range of product Harmony 9001SK

Product or component type Head for push-to-test pilot light

Light block supply Full voltage 120 V

Complementary

Bezel material Plastic

Mounting diameter 30 mm

Shape of signaling unit head Round

Cap/operator or lens colour Without cap

Light source Green LED

Bulb base BA 9s

Operating mode Push-to-test

[Us] rated supply voltage 120 V

Light source colour Green

Contacts type and composition 1 C/O

Size 30 mm

Light source LED

Environment

Protective treatment TC

IP degree of protection IP66

Packing Units

Unit Type of Package 1 PCE

Number of Units in Package 1 1

Package 1 Height 5.080 cm

Package 1 Width 5.842 cm

Package 1 Length 11.430 cm

Package 1 Weight 117.934 g



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture

Take-back	No
-----------	----