

Product data sheet

Specifications



KIT FLUSH-MOUNTING POUR ATV T5

NSYPTDS5

Product availability: Stock - Normally stocked in distribution facility

Main

Range	PanelSeT
Product or Component Type	Drive flush mounting kit
accessory category	Mounting and fixing accessory
Product Specific Application	Process and utilities
Range compatibility	Altivar variable speed drive ATV630 Altivar variable speed drive ATV930 PanelSeT SF and SM enclosures Altivar variable speed drive ATV340
compatibility for Altivar Process 630-930, size:	5
Motor power kW	30 kW 220/240 V 37 kW 220/240 V 45 kW 220/240 V 55 kW 380/480 V 75 kW 380/480 V 90 kW 380/480 V
Mounting location	1 back of enclosure mounting plate 2 inside enclosure
Kit composition	1 x mounting plate with flanges and integrated gasket, steel with anti-corrosive coating by screws and nuts 1 x fixing accessories 1 x drilling template 1 x instruction sheet 1 x edge protector profile, plastic 1 x fan support 1 x cover for fan protection

Complementary

Permanent permissible load	129.0 lb(US) (58.5 kg)
color	Gray RAL 7035)
Height	External: 38.4 in (975 mm) Cut-out: 36.2 in (920 mm)
Width	Cut-out: 15.0 in (380 mm) External: 16.8 in (427 mm)
Depth	Wall-enclosure separation : 8.09 in (205.5 mm)
Product Weight	24.440 lb(US) (11.086 kg)
Services	Configuration of enclosure pre-drilled back Factory installation drive flush mounting kit

Environment

IP degree of protection	IP55 conforming to IEC 60529
-------------------------	------------------------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US1CP4E22277
Discount Schedule	CP4E
GTIN	3606485442488
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	39.76 in (101.000 cm)
Package 1 Width	17.72 in (45.000 cm)
Package 1 Length	5.91 in (15.000 cm)
Package weight(Lbs)	24.440 lb(US) (11.086 kg)
Unit Type of Package 2	PAM
Number of Units in Package 2	20
Package 2 Height	65.35 in (166.000 cm)
Package 2 Width	39.37 in (100.000 cm)
Package 2 Length	47.24 in (120.000 cm)
Package 2 Weight	518.087 lb(US) (235.000 kg)

Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Environmental Disclosure

[Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	Ba0ee14c-eebb-47d8-a070-ade906247bb0
REACH Regulation	REACH Declaration

Use Again

Repack and remanufacture

Circularity Profile	No need of specific recycling operations
Take-back	No