

Product data sheet

Specifications



Indicator bank, Harmony XVB, illuminated unit, plastic, red, 70mm, integral flash discharge tube, 10joule, 24V AC/DC

XVBC8B4

To be discontinued

To be discontinued on: Jun 30, 2025

To be end-of-service on: Dec 31, 2026

Product availability: Stock - Normally stocked in distribution facility

Main

Range of Product	Harmony XVB Universal
Product or Component Type	Indicator bank
Beacon or indicator bank unit type	Illuminated unit
Signalling type	Flashing
Mounting diameter	2.8 in (70 mm)
Component name	XVBC
Material	Polycarbonate
Light source	Integral flash discharge tube, red
Bulb type	Flash discharge tube
[Us] rated supply voltage	24 V AC/DC
Flash energy	10 J

Complementary

Assembly style	Customer assembly, up to 5 units
Connections - terminals	Screw clamp terminals, <= 1 x 1.5 mm ² with cable end
[Ui] rated insulation voltage	250 V IEC 60947-1
Nominal voltage limit	0.85...1.1 Un IEC 60947-5-1
Current consumption	< 1300 mA AC < 850 mA DC
[Uiimp] rated impulse withstand voltage	4 kV IEC 60947-1
Flashing frequency	1 Hz
CAD overall width	2.8 in (70 mm)
CAD overall height	6.2 in (157 mm)
CAD overall depth	2.8 in (70 mm)
Product Weight	0.672 lb(US) (0.305 kg)

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Product Certifications	CCC EAC CSA C22-2 No 14 UL 508
Standards	IEC 60947-5-1
Protective treatment	TC
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Electrical shock protection class	Class I on support tube IEC 61140 Class II on base unit IEC 61140
IP degree of protection	IP65 on fixing base XVBZ0. IEC 60529 IP66 on base unit IEC 60529
NEMA degree of protection	Type 4X UL indoor)

Ordering and shipping details

Category	US100XV22611
Discount Schedule	00XV
GTIN	3389110845679
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.15 in (8.000 cm)
Package 1 Width	3.15 in (8.000 cm)
Package 1 Length	7.48 in (19.000 cm)
Package 1 Weight	11.323 oz (321.000 g)
Unit Type of Package 2	S03
Number of Units in Package 2	12
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	9.495 lb(US) (4.307 kg)

Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle)	211
--	-----

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	124e2d7a-5b1e-45ca-b93c-220dd91b55b6
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again


Repack and remanufacture

Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Dimensions Drawings

Indicator Bank with "Flash" Discharge Tube Unit**Dimensions**

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order to get **b** dimension.




- (1) Base unit XVBC07, to be ordered separately
- (2) Illuminated or audible signalling unit XVBC***, to be ordered separately
- (3) "Flash" unit

Number of illuminated or audible signalling units other than "flash" tube	b in mm	b in in.
1	295	11.61
2	358	14.09
3	421	16.57
4	484	19.06

Technical Illustration

Dimensions



Offer Marketing Illustration

Product benefits / Features

Features

Harmony XVB



- 3 types of light source:** 10-Watt incandescent bulb, built-in high-efficiency LEDs, 5 and 10-joule discharge tube
- 100,000 hours of maintenance-free lighting** thanks to "LED Protected" technology
- Connector with removable base, axial, or side cable entry,** immediate assembly, and fixing using a locking ring
- High degree of protection** (IP66) and Shock resistance (IK05)
- Fully flexible and interchangeable** construction of up to 5 lens units (six colors of light lens unit)

Offer Marketing Illustration

Product benefits / Features

Technical Benefits

Harmony XVB

Robust product performance with high IP protection and IK05 shock resistance



Greater loudness up to 90dB with continuous and intermittent tones



Conformity with International standards

Beacon lens on top with high intensity 5J, 10J Xenon flash, increase visibility from top and surrounding

Image of product / Alternate images

Alternative





Image of product in real life situation

