

Product data sheet

Specifications



Fuse carrier, TeSys DF, 1P, 30A, 600VAC, fuse class CC, blown fuse indicator

DFCC1V

Main

Range	TeSys
Product name	TeSys DF
Product or component type	Fuse carrier
Device short name	DFCC
Poles description	1P
Fuse type	, CC
Control type	Toggle padlockable
Local signalling	Blown fuse indication
Utilisation category	AC-20B conforming to IEC 60947-3
[Ue] rated operational voltage	600 V AC
[Ie] rated operational current	30 A
[Ui] rated insulation voltage	600 V AC
[Uiimp] rated impulse withstand voltage	6 kV
Short-circuit withstand	200 kA 600 V conforming to UL 512
Power dissipation in W	3 W maximum power dissipation by fuse

Complementary

Standards	UL 4248-1 UL 4248-4 CSA C22.2 No 4248-1 CSA C22.2 No 4248-4
Product certifications	UL recognized CSA
Mounting support	35 mm symmetrical DIN rail
Mounting position	Vertical (tolerance: +/- 23°)
Connections - terminals	Screw clamp terminals 1 cable(s) 1...16 mm ² rigid Screw clamp terminals 2 cable(s) 1...6 mm ² rigid Screw clamp terminals 1 cable(s) 1...16 mm ² flexible with or without Screw clamp terminals 2 cable(s) 1...6 mm ² flexible with or without
Tightening torque	2 N.m - with screwdriver PZ2 2 N.m - with screwdriver flat Ø 5.5 mm
Height	79.5 mm
Width	17.5 mm
Depth	61 mm
Product weight	0.042 kg

Quantity per set	Set of 12
------------------	-----------

Environment

Ambient air temperature for storage	-40...70 °C
Ambient air temperature for operation	-40...70 °C with derating above 20°C
Operating altitude	0...2000 m without derating
IP degree of protection	IP20
Pollution degree	3
Fire resistance	960 °C conforming to IEC 60695-2-1
Compatibility code	DFCC

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.200 cm
Package 1 Width	1.700 cm
Package 1 Length	6.400 cm
Package 1 Weight	44.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	6.800 cm
Package 2 Width	8.500 cm
Package 2 Length	22.200 cm
Package 2 Weight	570.000 g
Unit Type of Package 3	S03
Number of Units in Package 3	192
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	9.455 kg

Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Total lifecycle Carbon footprint 1

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard Yes

Packaging without single use plastic No

[EU RoHS Directive](#) Compliant

REACH Regulation [REACH Declaration](#)

California proposition 65 WARNING: Cancer - [www.P65Warnings.ca.gov](#)

Use Again

Repack and remanufacture

End of life manual availability No need of specific recycling operations

Take-back No

WEEE Label  The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Technical Illustration

Assembly's dimensions

