

Product data sheet

Specifications



set of 4 PanelSeT SM M12 lifting eyebolt - galvanized cast steel

NSYSMEB

Main

Area	PanelSeT
category	Lifting accessory
Product or component type	Lifting bracket Lifting eye
Application	Multi-purpose
Mounting location	Enclosure top
Range compatibility	PanelSeT PanelSeT SF PanelSeT PanelSeT SM
Device composition	4 eyebolt 4 fixing nuts
Quantity per set	Set of 1

Complementary

Material	Cast steel
Surface finish	Galvanized
Fixing mode	Screwed
Permanent permissible load	340 kg for 1 eyebolt vertical direction
Height	61.5 mm
Width	54 mm
Depth	26 mm
Diameter	29 mm
ISO thread	M12

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.000 cm
Package 1 Width	9.000 cm
Package 1 Length	14.500 cm
Package 1 Weight	1.058 kg
Unit Type of Package 2	PAM
Number of Units in Package 2	240
Package 2 Height	45.000 cm

Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	277.000 kg

Contractual warranty

Coverage	Core product
Warranty	18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Total lifecycle Carbon footprint	8
----------------------------------	---

Environmental Disclosure	Product Environmental Profile
--------------------------	---

Use Better

Materials and Substances

Packaging made with recycled cardboard	No
--	----

Packaging without single use plastic	No
--------------------------------------	----

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
-----------------------------------	--

REACH Regulation	REACH Declaration
------------------	-----------------------------------

Use Again

Repack and remanufacture

End of life manual availability	No need of specific recycling operations
---------------------------------	--

Take-back	No
-----------	----