

Product data sheet

Specifications



Wall mounted steel enclosure,
PanelSeT S3DC, plain door, without
plain chassis, 300x300x200mm,
IP66, IK10

NSYS3DC3320

Product availability: Stock - Normally stocked in distribution facility

Main

| | |
|-----------------------------|----------------------------|
| Range | PanelSeT |
| Product name | PanelSeT S3DC |
| Application | Multi-purpose |
| Category | Compact enclosure |
| Enclosure nominal height | 11.8 in (300 mm) |
| Enclosure nominal width | 11.8 in (300 mm) |
| Enclosure nominal depth | 7.9 in (200 mm) |
| Door type | Solid |
| Mounting plate description | Without mounting plate |
| Type of gland plate | Without gland plate |
| Installation accessory type | Wall-mounting |
| Device composition | 1 body 1 door 1 lock |

Complementary

| | |
|-----------------------------|---|
| body type | Single piece body Gutter-shaped front profile double sheet thickness |
| Number of doors | Front face 1 |
| Door opening side | Reversible 120 °) |
| Lock type | Screw driver insert lock |
| Accessibility for operation | Front |
| Removable parts | Door by hinges |
| Material | steel |
| Surface finish | epoxy-polyester powder |
| color | Gray RAL 7035) |
| Standards | IEC 62208 UL CUL |
| Product Certifications | UL |
| Product Weight | 9.938 lb(US) (4.508 kg) |

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| | |
|---------------------------|----------------|
| NEMA Degree of Protection | NEMA 4X/13 |
| IK degree of protection | IK10 IEC 62262 |
| IP degree of protection | IP66 IEC 60529 |

Ordering and shipping details

| | |
|-------------------|---------------|
| Category | US10ES180034 |
| Discount Schedule | 0ES1 |
| GTIN | 3606480313998 |
| Returnability | Yes |
| Country of origin | FR |

Packing Units

| | |
|------------------------------|-----------------------------|
| Unit Type of Package 1 | PCE |
| Nbr. of units in pkg. | 1 |
| Package 1 Height | 9.84 in (25.000 cm) |
| Package 1 Width | 12.99 in (33.000 cm) |
| Package 1 Length | 15.75 in (40.000 cm) |
| Package weight(Lbs) | 11.023 lb(US) (5.000 kg) |
| Unit Type of Package 2 | PAM |
| Number of Units in Package 2 | 48 |
| Package 2 Height | 55.91 in (142.000 cm) |
| Package 2 Width | 39.37 in (100.000 cm) |
| Package 2 Length | 47.24 in (120.000 cm) |
| Package 2 Weight | 562.179 lb(US) (255.000 kg) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

| | |
|--|---|
| Carbon footprint (kg CO2 eq, Total Life cycle) | 47 |
| Environmental Disclosure | Product Environmental Profile |

Use Better

Materials and Substances

| | |
|--|--|
| Packaging made with recycled cardboard | No |
| Packaging without single use plastic | No |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| SCIP Number | E893f0a0-d2cc-4011-9425-3873dde70142 |
| REACH Regulation | REACH Declaration |

Use Again

Repack and remanufacture

| | |
|---------------------|--|
| Circularity Profile | No need of specific recycling operations |
| Take-back | No |