

# Product data sheet

Specifications



variable speed drive, SFlex Altivar  
212, 460V AC, 3 phase, 30hp,  
enclosed drive

SFD212MG4YB07D07

Product availability: Stock - Normally stocked in distribution facility

## Main

Product or Component Type	Variable speed drive
Motor power kW	22 kW
Maximum Horse Power Rating	30 kW
Nominal output current	40 A 460 V

## Ordering and shipping details

Category	US1CP4D22199
Discount Schedule	CP4D
GTIN	785901456308
Returnability	Yes
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	27.52 in (69.9 cm)
Package 1 Width	35.59 in (90.4 cm)
Package 1 Length	70.98 in (180.3 cm)
Package weight(Lbs)	253.0005 lb(US) (114.759 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Use Better

#### Materials and Substances

Packaging made with recycled cardboard	No
--	----

Packaging without single use plastic	No
--------------------------------------	----

### Use Again

#### Repack and remanufacture

Take-back	No
-----------	----