

Product data sheet

Specifications



LED bulb, Harmony XVB, BA 15d, yellow, steady light, 24V AC/DC

DL1BDB8

⚠ To be discontinued on: Jun 30, 2025

⚠ To be end-of-service on: Dec 31, 2026

⚠ To be discontinued

Product availability: Stock - Normally stocked in distribution facility

Main

| | |
|---------------------------------------|---|
| Range Compatibility | Harmony XVP Harmony XVB Harmony XVD |
| Accessory / separate part designation | Protected LED bulb |
| Accessory / Separate Part Type | LED bulb |
| Accessory / separate part category | Lighting accessories |
| Accessory / separate part destination | Beacon and indicator bank |
| [Us] rated supply voltage | 24 V AC/DC |
| Signalling type | Steady |
| Signalling colour | Yellow |
| Sale per indivisible quantity | 1 |

Complementary

| | |
|---------------------|-------------------------|
| Current Consumption | 47 mA |
| Bulb base | BA 15d |
| Product Weight | 0.033 lb(US) (0.015 kg) |

Ordering and shipping details

| | |
|-------------------|---------------|
| Category | US100XV22611 |
| Discount Schedule | 00XV |
| GTIN | 3389110118049 |
| Returnability | Yes |
| Country of origin | ID |

Packing Units

| | |
|------------------------------|---------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 2.24 in (5.700 cm) |
| Package 1 Width | 1.77 in (4.500 cm) |
| Package 1 Length | 1.38 in (3.500 cm) |
| Package 1 Weight | 0.388 oz (11.000 g) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| | |
|-------------------------------------|-------------------------|
| Unit Type of Package 2 | S01 |
| Number of Units in Package 2 | 60 |
| Package 2 Height | 5.91 in (15.000 cm) |
| Package 2 Width | 5.91 in (15.000 cm) |
| Package 2 Length | 15.75 in (40.000 cm) |
| Package 2 Weight | 2.297 lb(US) (1.042 kg) |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty | 18 months |
|-----------------|-----------|



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle)

34

Use Better

Materials and Substances

Packaging made with recycled cardboard

Yes

Packaging without single use plastic

Yes

[EU RoHS Directive](#)

Pro-active compliance (Product out of EU RoHS legal scope)

REACH Regulation

[REACH Declaration](#)

California proposition 65

WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](#)

Use Again

Repack and remanufacture

Circularity Profile

No need of specific recycling operations

Take-back

No

WEEE

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Offer Marketing Illustration

Product benefits / Features

Features

Harmony XVB



- 3 types of light source: 10-Watt incandescent bulb, built-in high-efficiency LEDs, 5 and 10-joule discharge tube
- 100,000 hours of maintenance-free lighting thanks to "LED Protected" technology
- Connector with removable base, axial, or side cable entry, immediate assembly, and fixing using a locking ring
- High degree of protection (IP66) and Shock resistance (IK05)
- Fully flexible and interchangeable construction of up to 5 lens units (six colors of light lens unit)

Offer Marketing Illustration

Product benefits / Features

Technical Benefits

Harmony XVB

Robust product performance with high IP protection and IK05 shock resistance



Greater loudness up to 90dB with continuous and intermittent tones



Conformity with International standards

Beacon lens on top with high intensity 5J, 10J Xenon flash, increase visibility from top and surrounding

Image of product / Alternate images

Alternative





