

Product data sheet

Characteristics

8910DPA34V14

Contactor, Definite Purpose, 30A, 4 pole, 20 HP at 575 VAC, 3 phase, 24/24 VAC 50/60 Hz coil, open



Main

Product or Component Type	Definite Purpose Contactor
Line Rated Current	30 A
Number of Poles	4P
Pole contact composition	4 NO
Range of Product	DPA

Complementary

Maximum Horse Power Rating	2 Hp 115 V AC, 1 phase 5 Hp 230 V AC, 1 phase 10 Hp 230 V AC, 3 phase 15 Hp 460 V AC, 3 phase 20 hp 575 V AC, 3 phase
Locked rotor rated current	150 A 460 V AC 120 A 575 V AC 180 A 277 V AC
[Ue] rated operational voltage	600 V AC
[Uc] control circuit voltage	24 V AC 50/60 Hz
Phase	3 phase
Electrical Connection	Quick connect terminals Binder head

Environment

Product Certifications	UL Recognized CSA
------------------------	----------------------

Ordering and shipping details

Category	21343-8910 DPA 3_(30 AMP)
Discount Schedule	CP1B
GTIN	785901073512
Nbr. of units in pkg.	1
Package weight(Lbs)	20.96 oz (594.206 g)
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.10 in (7.874 cm)
Package 1 width	4.10 in (10.414 cm)
Package 1 Length	3.20 in (8.128 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Weight	12.00 lb(US) (5.443 kg)

Package 2 Height	7.00 in (17.78 cm)
Package 2 width	6.90 in (17.526 cm)
Package 2 Length	8.40 in (21.336 cm)

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------