

# Product data sheet

## Characteristics

# 8910DPA53V06

Contactor, Definite Purpose, 50A, 3 pole, 30 HP at 575 VAC, 3 phase, 440/480 VAC 50/60 Hz coil, open



### Main

Product or Component Type	Definite Purpose Contactor
Line Rated Current	50 A
Number of Poles	3P
Pole contact composition	3 NO
Range of Product	DPA

### Complementary

Maximum Horse Power Rating	3 Hp 115 V AC, 1 phase 10 Hp 230 V AC, 1 phase 15 Hp 230 V AC, 3 phase 30 Hp 460 V AC, 3 phase 30 hp 575 V AC, 3 phase
Locked rotor rated current	300 A 277 V AC 250 A 460 V AC 200 A 575 V AC
[Ue] rated operational voltage	600 V AC
[Uc] control circuit voltage	440 V AC 50 Hz 480 V AC 60 Hz
Phase	3 phase
Electrical Connection	Quick connect terminals Box lugs

### Environment

Product Certifications	UL Recognized CSA
------------------------	----------------------

### Ordering and shipping details

Category	21345-8910 DPA 5_(50 AMP)
Discount Schedule	CP1B
GTIN	785901081128
Returnability	Yes
Country of origin	CN

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.70 in (6.858 cm)
Package 1 Width	3.80 in (9.652 cm)
Package 1 Length	4.30 in (10.922 cm)
Package 1 Weight	25.44 oz (721.212 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	8

Package 2 Height	8.20 in (20.828 cm)
Package 2 Width	5.90 in (14.986 cm)
Package 2 Length	9.00 in (22.86 cm)
Package 2 Weight	13.06 lb(US) (5.924 kg)

### Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 Yes

### Contractual warranty

Warranty	18 months
----------	-----------

Approximate Dimensions

Electrical Clearance/Wire Bending Space

