

# Product data sheet

## Characteristics

# 8910DPA62V02

Contactor, Definite Purpose, 60A, 2 pole, 10 HP at 230 VAC, 1 phase, 110/120 VAC 50/60 Hz coil, open



### Main

Product or Component Type	Definite Purpose Contactor
Line Rated Current	60 A
Number of Poles	2P
Pole contact composition	2 NO
Range of Product	DPA

### Complementary

Maximum Horse Power Rating	5 Hp 115 V AC, 1 phase 10 hp 230 V AC, 1 phase
Locked rotor rated current	360 A 277 V AC 300 A 460 V AC 240 A 575 V AC
[Ue] rated operational voltage	600 V AC
[Uc] control circuit voltage	120 V AC 60 Hz 110 V AC 50 Hz
Phase	1 phase
Electrical Connection	Quick connect terminals Box lugs

### Environment

Product Certifications	UL Recognized CSA
------------------------	----------------------

### Ordering and shipping details

Category	21346-8910 DPA 6_(60 AMP)
Discount Schedule	CP1B
GTIN	785901080824
Returnability	Yes
Country of origin	CN

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.80 in (9.652 cm)
Package 1 Width	4.50 in (11.43 cm)
Package 1 Length	2.70 in (6.858 cm)
Package 1 Weight	23.36 oz (662.245 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Height	8.10 in (20.574 cm)
Package 2 Width	5.70 in (14.478 cm)

---

Package 2 Length	9.00 in (22.86 cm)
Package 2 Weight	12.05 lb(US) (5.466 kg)

---

#### Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 Yes

---

#### Contractual warranty

Warranty	18 months
----------	-----------

---

Approximate Dimensions

