

# Product data sheet

## Characteristics

# 8910DPA73RV09

Contactor, Definite Purpose, 75A, 3 pole, 40 HP at 575 VAC, 3 phase, 208/240 VAC 60 Hz 220 VAC 50 Hz coil, open



### Main

Product or Component Type	Definite Purpose Contactor
Line Rated Current	75 A
Number of Poles	3P
Pole contact composition	3 NO
Range of Product	DPA

### Complementary

Maximum Horse Power Rating	5 Hp 115 V AC, 1 phase 15 Hp 230 V AC, 1 phase 25 Hp 230 V AC, 3 phase 40 Hp 460 V AC, 3 phase 40 hp 575 V AC, 3 phase
Locked rotor rated current	450 A 277 V AC 375 A 460 V AC 300 A 575 V AC
[Ue] rated operational voltage	600 V AC
[Uc] control circuit voltage	208...240 V AC 60 Hz 220 V AC 50 Hz
Phase	3 phase
Electrical Connection	Quick connect terminals Box lugs
Height	3.65 in (92.8 mm)
Width	4.10 in (104.03 mm)
Depth	2.56 in (65 mm)

### Environment

Product Certifications	UL Recognized CSA
------------------------	----------------------

### Ordering and shipping details

Category	21347-8910 DPA 7_(70 AMP)
Discount Schedule	CP1B
GTIN	785901768371
Returnability	Yes

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.06 in (10.3 cm)
Package 1 Width	3.35 in (8.5 cm)
Package 1 Length	3.66 in (9.3 cm)
Package 1 Weight	24.00 oz (680.4 g)

## Offer Sustainability

---

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

---

## Contractual warranty

---

Warranty	18 months
----------	-----------

---