

Product data sheet

Characteristics

8910DPAG63V02

Contactor, Definite Purpose, 60A, 3 pole, 30 HP at 575 VAC, 3 phase, 110/120 VAC 50/60 Hz coil, NEMA 1



Main

| | |
|---------------------------|----------------------------|
| Product or Component Type | Definite Purpose Contactor |
| Line Rated Current | 60 A |
| Number of Poles | 3P |
| Pole contact composition | 3 NO |
| Range of Product | DPA |
| Provided equipment | Enclosure |
| Enclosure Type | NEMA type 1 |

Complementary

| | |
|--------------------------------|--|
| Maximum Horse Power Rating | 5 Hp 115 V AC, 1 phase 10 Hp 230 V AC, 1 phase 30 Hp 460 V AC, 3 phase 30 Hp 575 V AC, 3 phase 25 hp 230 V AC, 3 phase |
| Locked rotor rated current | 360 A 277 V AC 300 A 460 V AC 240 A 575 V AC |
| [Ue] rated operational voltage | 600 V AC |
| [Uc] control circuit voltage | 120 V AC 60 Hz 110 V AC 50 Hz |
| Phase | 3 phase |
| Electrical Connection | Box lugs Quick connect terminals |
| Height | 12.69 in (322.33 mm) |
| Width | 27.81 in (706.37 mm) |
| Depth | 6.31 in (160.27 mm) |

Environment

| | |
|------------------------|----------------------|
| Product Certifications | UL Recognized CSA |
|------------------------|----------------------|

Ordering and shipping details

| | |
|-------------------|---------------------------|
| Category | 21346-8910 DPA 6_(60 AMP) |
| Discount Schedule | CP1B |
| GTIN | 785901325277 |
| Returnability | Yes |
| Country of origin | CN |

Packing Units

| | |
|------------------------------|-----------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 7.20 in (18.288 cm) |
| Package 1 Width | 9.00 in (22.86 cm) |
| Package 1 Length | 13.40 in (34.036 cm) |
| Package 1 Weight | 8.40 lb(US) (3.81 kg) |

Offer Sustainability

| | |
|----------------------------|---|
| REACH Regulation |  REACH Declaration |
| EU RoHS Directive | Compliant  EU RoHS Declaration |
| Mercury free | Yes |
| China RoHS Regulation |  China RoHS Declaration |
| RoHS exemption information |  Yes |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|