

Product data sheet

Characteristics

8911DPSG13V02

Starter, Definite Purpose, nonreversing, 20A,
3 pole, 3 phase, 120 VAC coil, melting alloy
overload, NEMA 1, +options



Main

Product	Definite Purpose Starter
Ampere Rating	20 A
Horsepower Rating	3 Hp 230 V AC, 1 phase 7.5 Hp 230 V AC, 3 phase 1.5 Hp 115 V AC, 1 phase 7.5 Hp 460 V AC, 3 phase 7.5 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Phase	3 phase

Complementary

Enclosure Material	Painted sheet steel
Enclosure Rating	NEMA 1
Locked Rotor Amperes	120 A 230 V AC 100 A 460 V AC 80 A 575 V AC
Number of Poles	3P
Range	DPS
Overload Type	Melting alloy
Number of Thermal Units	3

Ordering and shipping details

Category	21381-8911 DP
Discount Schedule	CP1
GTIN	785901081470
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.40 in (16.256 cm)
Package 1 Width	6.80 in (17.272 cm)
Package 1 Length	10.60 in (26.924 cm)
Package 1 Weight	5.64 lb(US) (2.558 kg)

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------