



### Main

Product	Definite Purpose Starter
Ampere Rating	40 A
Horsepower Rating	3 Hp 115 V AC, 1 phase 10 Hp 230 V AC, 3 phase 7.5 Hp 230 V AC, 1 phase 20 Hp 460 V AC, 3 phase 25 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Circuit Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Phase	3 phase

### Complementary

Enclosure Rating	Not rated (open device)
Locked Rotor Amperes	240 A 230 V AC 200 A 460 V AC 160 A 575 V AC
Number of Poles	3P
Range	DPS
Overload Type	Melting alloy
Number of Thermal Units	3

### Ordering and shipping details

Category	21381-8911 DP
Discount Schedule	CP1
GTIN	785901150879
Returnability	No
Country of origin	CN

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.00 in (12.7 cm)
Package 1 Width	4.80 in (12.192 cm)
Package 1 Length	8.00 in (20.32 cm)
Package 1 Weight	32.00 oz (907.185 g)

### Offer Sustainability

REACH Regulation	<input checked="" type="checkbox"/> REACH Declaration
EU RoHS Directive	Compliant <input checked="" type="checkbox"/> EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	<input checked="" type="checkbox"/> China RoHS Declaration
RoHS exemption information	<input checked="" type="checkbox"/> Yes

### Contractual warranty

Warranty	18 months
----------	-----------