



### Main

Product or Component Type	Reversing Hoist Contactor
Line Rated Current	40 A
Maximum Horse Power Rating	10 Hp 230 V AC, 3 phase 3 Hp 115 V AC, 1 phase 7.5 Hp 230 V AC, 1 phase 20 Hp 460 V AC, 3 phase 20 hp 575 V AC, 3 phase

### Complementary

Product Certifications	UL Listed CSA
[Ue] rated operational voltage	600 V AC
Poles description	4P
[Uc] control circuit voltage	110 V AC 50 Hz 120 V AC 60 Hz
Phase	3 phase
Range of Product	DPR

### Ordering and shipping details

Category	21403-8965DPR1>DPR4 - 20A>40A REV HOIST
Discount Schedule	CP1
GTIN	785901168959
Returnability	No
Country of origin	CN

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.00 in (12.7 cm)
Package 1 Width	5.00 in (12.7 cm)
Package 1 Length	7.40 in (18.796 cm)
Package 1 Weight	4.00 lb(US) (1.814 kg)

### Offer Sustainability

REACH Regulation	<input checked="" type="checkbox"/> REACH Declaration
EU RoHS Directive	Compliant <input checked="" type="checkbox"/> EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	<input checked="" type="checkbox"/> China RoHS Declaration
RoHS exemption information	<input checked="" type="checkbox"/> Yes

### Contractual warranty

Warranty	18 months
----------	-----------