

Product data sheet

Characteristics

9001K2L1R20H13

Illuminated push-button, Harmony 9001K, metal, mushroom 35mm, red, 30mm, spring return, 110-120V, 1 C/O



Main

| | |
|---------------------------------|-------------------------|
| Range of Product | Harmony 9001K |
| Product or Component Type | Illuminated push-button |
| Device short name | K |
| Type of operator | Spring return |
| Operator profile | Red projecting |
| Operator additional information | Screw-on plastic |

Complementary

| | |
|--------------------------------|----------------------------|
| Bezel material | Metal |
| Mounting diameter | 1.18 in (30 mm) |
| Light source | incandescent |
| Light source | Incandescent bulb |
| Bulb base | BA 9s |
| Light block supply | Via integral transformer |
| [Us] rated supply voltage | 110...120 V AC |
| Contacts type and composition | 1 C/O |
| Connections - terminals | Screw clamp terminals |
| Operating position | Any position |
| [Ie] rated operational current | 10 A, AC-15 10 A, DC-13 |
| Contact operation | Standard |
| Device presentation | Complete product |
| Cap/operator or lens colour | Red |
| [Us] rated supply voltage | 110...120 V |
| Light block supply | Via integral transformer |
| Operator profile | Mushroom Ø 35 mm |
| Type of operator | Spring return |
| Supply frequency | 50...60 Hz |
| Size | 30 mm |

Environment

| | |
|---------------------------|--|
| Product Certifications | UL listed file E42259 CCN NKCR CSA LR 25490 class 3211 03 CE NEMA |
| NEMA degree of protection | NEMA 1/2/3/3R/4/6/12/13 |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

| | |
|-------------------|-----------------------------|
| Category | 21426-9001 K (NOT KA,KM,KX) |
| Discount Schedule | CS1 |
| GTIN | 785901027911 |
| Returnability | No |
| Country of origin | MX |

Packing Units

| | |
|------------------------------|----------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 5.08 in (12.903 cm) |
| Package 1 Width | 2.00 in (5.08 cm) |
| Package 1 Length | 12.90 in (32.774 cm) |
| Package 1 Weight | 9.44 oz (267.62 g) |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation |  REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Mercury free | Yes |
| China RoHS Regulation |  China RoHS Declaration |
| RoHS exemption information |  Yes |
| Environmental Disclosure |  Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|