

Product data sheet

Characteristics

9001KR8P1LGGH25

30mm push button, Type K, green illuminated momentary push pull mushroom, 120VAC green LED, 1NO/1NC contact, NEMA 4, 13



Main

Range of Product	Harmony 9001K
Product or Component Type	Illuminated push-button
Device short name	K
Operator additional information	Screw-on plastic

Complementary

Bezel material	Metal
Mounting diameter	1.18 in (30 mm)
Light source	LED
Bulb base	BA 9s
Light block supply	Without supply
Contacts type and composition	1 NC late break + 1 NC
[Ie] rated operational current	10 A, AC-15 10 A, DC-13
Contact operation	Late-break
Device presentation	Complete product

Environment

Product Certifications	CE CSA LR 25490 class 3211 03 NEMA UL listed file E42259 CCN NKCR
NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13

Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	785901760979
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.91 in (15 cm)
Package 1 Width	5.83 in (14.8 cm)
Package 1 Length	15.67 in (39.8 cm)
Package 1 Weight	8.00 oz (226.796 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------