



**Main**

Range of Product	Harmony 9001KY
Product or Component Type	Control station
Device short name	9001KY
Provided equipment	Label plate OPEN-CLOSE
Contact block name	KA1
Product Specific Application	For hoisting and mechanical handling applications
Level or class	Class III Class II Division 2 Group G

**Complementary**

Enclosure/cubicle description	Wall-mounted enclosure 2 cut-outs Ø 30 mm
Enclosure material	Die cast zinc alloy Gray
Type of Installation	Indoor/outdoor
Control station composition	2 push-buttons 2 NO + 2 NC
Mechanical interlocking	Without mechanical interlock
Connector Type	Screw clamp connector
Connections - terminals	Direct connection AWG 2) solid stranded Direct connection AWG 12) solid stranded Direct connection AWG 24) solid stranded
[Ue] rated operational voltage	300 V
[Ie] rated operational current AC	10 A

**Environment**

NEMA degree of protection	NEMA 4 NEMA 3 NEMA 1 NEMA 13
Environmental characteristic	Resistant against immersion in water Dust and oil resistant
Product Certifications	UL Listed
Ambient Air Temperature for Operation	-13...140 °F (-25...60 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)

**Ordering and shipping details**

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	785901039990
Returnability	No
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.97 in (35.484 cm)
Package 1 Width	5.50 in (13.97 cm)
Package 1 Length	35.48 in (90.129 cm)
Package 1 Weight	4.00 lb(US) (1.814 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------