

Product data sheet

Characteristics

9001SKY203

30mm push button, Type SK, control station, START and STOP, 6A inductive at 120VAC, lock out on STOP, NEMA 4, 4X



Main

Range of Product	Harmony 9001KY
Product or Component Type	Control station
Device short name	9001SK
Provided equipment	Label plate START-STOP
Contact block name	KA1 KA3

Complementary

Enclosure/cubicle description	Wall-mounted enclosure 2 cut-outs
Enclosure material	Polymeric
Type of Installation	Indoor/outdoor
Control station composition	2 push-buttons 1 NO + 2 NC
Connector Type	Screw clamp connector
[Ue] rated operational voltage	600 V
[Ie] rated operational current AC	10 A

Environment

NEMA degree of protection	NEMA 4 NEMA 3 NEMA 1 NEMA 13
Environmental characteristic	Resistant against immersion in water Dust and oil resistant
Product Certifications	CSA LR25490 class 3211 03 CE UL listed file E42259 CCN NKCR
Ambient Air Temperature for Operation	-13...140 °F (-25...60 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)

Ordering and shipping details

Category	21429-9001 SK,SKY
Discount Schedule	CS1
GTIN	785901044604
Returnability	No
Country of origin	MX

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.16 in (25.806 cm)
Package 1 Width	4.00 in (10.16 cm)
Package 1 Length	25.81 in (65.548 cm)
Package 1 Weight	34.56 oz (979.76 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------