

Product data sheet

Specifications



TeSys Deca Manual Starter and Protector, auxiliary contact block, 1 NO and 1 NC, side mount, screw clamp

GVAN11

Product availability: Stock - Normally stocked in distribution facility

Main

Range	TeSys TeSys Deca
Device short name	GVAN
Product or Component Type	Auxiliary contact block
Product Compatibility	GV2ME GV2RT GV2L GV3P GV3L GV2LE GV2P
Mounting Location	Left side
Pole contact composition	1 NO + 1 NC

Complementary

[Ui] rated insulation voltage	600 V UL 508 690 V IEC 60947-1 600 V CSA C22.2 No 14
[Ue] rated operational voltage	48...690 V AC 24...240 V DC
[Ith] conventional free air thermal current	6 A
Mechanical durability	100000 cycles
Minimum switching current	5 mA
Minimum switching voltage	17 V
Protection type	GB2CB... circuit breaker GG fuse 10 A
Rated operational power in VA	300 VA 48 V AC-15 100000 cycles 414 VA 690 V AC-15 100000 cycles 500 VA 110...127 V AC-15 100000 cycles 500 VA 500 V AC-15 100000 cycles 650 VA 440 V AC-15 100000 cycles 720 VA 230...240 V AC-15 100000 cycles 850 VA 380...415 V AC-15 100000 cycles
Rated operational power in W	120 W 240 V DC-13 100000 cycles 140 W 110 V DC-13 100000 cycles 140 W 24 V DC-13 100000 cycles 180 W 60 V DC-13 100000 cycles 240 W 48 V DC-13 100000 cycles
Tightening torque	12.4 lbf.in (1.4 N.m) screw clamp terminals
Height	3.5 in (89 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Width	0.4 in (9.3 mm)
Depth	2.6 in (66 mm)
Product Weight	0.11 lb(US) (0.05 kg)
color	Dark grey

Environment

Environmental characteristic	Normal environment
Product Certifications	UKCA

Ordering and shipping details

Category	US10I1122367
Discount Schedule	0I11
GTIN	3389110343489
Returnability	Yes
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	0.59 in (1.500 cm)
Package 1 Width	2.76 in (7.000 cm)
Package 1 Length	3.54 in (9.000 cm)
Package weight(Lbs)	1.623 oz (46.000 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	3.74 in (9.500 cm)
Package 2 Width	3.94 in (10.000 cm)
Package 2 Length	5.98 in (15.200 cm)
Package 2 Weight	17.989 oz (510.000 g)
Unit Type of Package 3	S02
Number of Units in Package 3	60
Package 3 Height	5.91 in (15.000 cm)
Package 3 Width	11.81 in (30.000 cm)
Package 3 Length	15.75 in (40.000 cm)
Package 3 Weight	7.262 lb(US) (3.294 kg)

Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO₂ eq, Total Life cycle) **1**

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard **Yes**

Packaging without single use plastic **No**

[EU RoHS Directive](#) **Compliant**

California proposition 65 **WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to [www.P65Warnings.ca.gov](#)**

Use Again

Repack and remanufacture


Circularity Profile [End of Life Information](#)

Take-back **No**

WEEE Label The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Connections and Schema

GVAN11



Technical Illustration

Assembly's dimensions

