

Product data sheet

Specifications



variable speed drive, Sflex Altivar
212, 460V AC, 3 phase, 100hp,
enclosed drive, bypass, LINECONT,
L

SFD212SG4YB07D07

Product availability: Stock - Normally stocked in distribution facility

Main

Product or Component Type	Variable speed drive
Motor power kW	75 kW
Maximum Horse Power Rating	100 hp
Nominal output current	124 A 460 V

Ordering and shipping details

Category	US1CP4D22199
Discount Schedule	CP4D
GTIN	785901116417
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	27.80 in (70.6 cm)
Package 1 Width	35.98 in (91.4 cm)
Package 1 Length	71.50 in (181.6 cm)
Package weight(Lbs)	342.001 lb(US) (155.129 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No

Use Again

 Repack and remanufacture	
Take-back	No