



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Cable length	6 ft (1.83 m)
Product Compatibility	KVM Switch

Physical

Color	Black Blue Green
Height	0.51 in (1.3 cm)
Width	0.98 in (2.5 cm)
Depth	0.51 in (1.3 cm)
Net Weight	0.15 lb(US) (0.07 kg)
Mounting Support	Hidden
Mounting Mode	Not rack-mountable
Connector B	SUB-D 15HD male VGA Monitor
Connector A	USB 2.0 type A male

Ordering and shipping details

GTIN	731304278825
Package weight(Lbs)	0.18 lb(US) (0.08 kg)

Packing Units

Package 1 Height	1.97 in (5 cm)
Package 1 width	6.50 in (16.5 cm)
Package 1 Length	9.25 in (23.5 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------