



### Overview

Lead time	Usually in Stock
-----------	------------------

### Main

Main Input Voltage	230 V
Main Output Voltage	230 V
Input Connection Type	IEC 60309 32 A 2P+E
Number of rack unit	0U
Cable length	10 ft (3.05 m)
Number of cables	1
Provided Equipment	Installation guide Safety guide

### Physical

Height	64.02 in (162.6 cm)
Width	2.20 in (5.6 cm)
Depth	1.69 in (4.3 cm)
Net Weight	13.62 lb(US) (6.18 kg)
Mounting Location	Side
Mounting preference	No preference
Mounting Mode	Not rack-mountable

### Input

Acceptable Input Voltage	200...240 V
Input current limits	32 A
Load Capacity	7400 VA
Input Frequency	50/60 Hz

### Output

Number of power socket outlets	20 IEC 60320 C13 6 IEC 60320 C19
--------------------------------	-------------------------------------

### Conformance

Product Certifications	CE EAC IRAM VDE
------------------------	--------------------------

## Environmental

Ambient Air Temperature for Operation	32...122 °F (0...50 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...149 °F (-15...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

## Ordering and shipping details

GTIN	731304327783
Package weight(Lbs)	17.64 lb(US) (8 kg)

## Packing Units

Package 1 Height	73.82 in (187.5 cm)
Package 1 width	8.90 in (22.6 cm)
Package 1 Length	5.31 in (13.5 cm)
Number of Units in Package 3	35

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Lead free	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------