



### Overview

|              |                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
|--------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Presentation | Free up space and secure power cords between rack-mount PDUs and attached IT equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads. |
| Lead time    | Usually in Stock                                                                                                                                                                                                                                                                                                                                                                                                                                                      |

### Main

|                    |                                                         |
|--------------------|---------------------------------------------------------|
| Plug standard      | IEC 60320 C14                                           |
| Cable length       | 6 ft (1.83 m)                                           |
| Number of cables   | 6                                                       |
| Provided Equipment | 3 Left-angle jumper cords<br>3 Right-angle jumper cords |

### Physical

|                     |                       |
|---------------------|-----------------------|
| Color               | Black                 |
| Height              | 9.45 in (24 cm)       |
| Width               | 2.95 in (7.5 cm)      |
| Depth               | 2.17 in (5.5 cm)      |
| Net Weight          | 2.98 lb(US) (1.35 kg) |
| Mounting preference | No preference         |
| Mounting Mode       | Not rack-mountable    |

### Input

|                      |      |
|----------------------|------|
| Max line current     | 10 A |
| Input current limits | 10 A |

### Output

|                                      |                 |
|--------------------------------------|-----------------|
| Maximum Total Current Draw per Phase | 10 A            |
| Number of power socket outlets       | 1 IEC 60320 C13 |
| Cord Length                          | 6 ft (1.83 m)   |

### Conformance

|                        |                  |
|------------------------|------------------|
| Product Certifications | CSA<br>UL Listed |
|------------------------|------------------|

## Environmental

|                                       |                                  |
|---------------------------------------|----------------------------------|
| Ambient Air Temperature for Operation | 32...221 °F (0...105 °C)         |
| Relative Humidity                     | 20...80 %                        |
| Operating altitude                    | 0...10000 ft                     |
| Ambient Air Temperature for Storage   | -13...221 °F (-25...105 °C)      |
| Storage Relative Humidity             | 20...80 %                        |
| Storage altitude                      | 0...50000 ft (0.00...15240.00 m) |

## Ordering and shipping details

|                     |                       |
|---------------------|-----------------------|
| GTIN                | 731304294399          |
| Package weight(Lbs) | 2.98 lb(US) (1.35 kg) |

## Packing Units

|                              |                  |
|------------------------------|------------------|
| Package 1 Height             | 9.45 in (24 cm)  |
| Package 1 width              | 2.95 in (7.5 cm) |
| Package 1 Length             | 2.17 in (5.5 cm) |
| Number of Units in Package 3 | 300              |

## Offer Sustainability

|                           |                                                                                                                                                                                                                                                    |
|---------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status  | Green Premium product                                                                                                                                                                                                                              |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation          | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                  |
| EU RoHS Directive         | Compliant <a href="#">EU RoHS Declaration</a>                                                                                                                                                                                                      |
| Lead free                 | Yes                                                                                                                                                                                                                                                |
| Environmental Disclosure  | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                      |
| Circularity Profile       | <a href="#">End Of Life Information</a>                                                                                                                                                                                                            |
| Take-back                 | Take-back program available                                                                                                                                                                                                                        |

## Contractual warranty

|          |                           |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|