



Overview

Lead time	Usually in Stock
-----------	------------------

Physical

Color	Red
Height	9.45 in (24 cm)
Width	2.95 in (7.5 cm)
Depth	2.17 in (5.5 cm)
Net Weight	2.98 lb(US) (1.35 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Conformance

Product Certifications	CSA UL Listed
------------------------	------------------

Environmental

Ambient Air Temperature for Operation	32...221 °F (0...105 °C)
Relative Humidity	20...80 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...221 °F (-25...105 °C)
Storage Relative Humidity	20...80 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	731304319696
Package weight(Lbs)	2.98 lb(US) (1.35 kg)

Packing Units

Package 1 Height	9.45 in (24 cm)
Package 1 width	2.95 in (7.5 cm)
Package 1 Length	2.17 in (5.5 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------