



## Overview

|           |                  |
|-----------|------------------|
| Lead time | Usually in Stock |
|-----------|------------------|

## Main

|                       |               |
|-----------------------|---------------|
| Input Connection Type | IEC 60320 C20 |
| Cable length          | 4 ft (1.22 m) |
| Number of cables      | 6             |

## Physical

|                     |                       |
|---------------------|-----------------------|
| Color               | Red                   |
| Height              | 11.81 in (30 cm)      |
| Width               | 2.76 in (7 cm)        |
| Depth               | 2.76 in (7 cm)        |
| Net Weight          | 3.62 lb(US) (1.64 kg) |
| Mounting preference | No preference         |
| Mounting Mode       | Not rack-mountable    |

## Input

|                      |      |
|----------------------|------|
| Max line current     | 16 A |
| Input current limits | 16 A |

## Output

|                                      |                 |
|--------------------------------------|-----------------|
| Maximum Total Current Draw per Phase | 16 A            |
| Number of power socket outlets       | 1 IEC 60320 C19 |
| Cord Length                          | 4 ft (1.22 m)   |

## Conformance

|                        |                                       |
|------------------------|---------------------------------------|
| Product Certifications | CCC<br>CSA<br>PSE<br>UL Listed<br>VDE |
|------------------------|---------------------------------------|

## Environmental

|                                       |                                  |
|---------------------------------------|----------------------------------|
| Ambient Air Temperature for Operation | 32...167 °F (0...75 °C)          |
| Relative Humidity                     | 20...80 %                        |
| Operating altitude                    | 0...10000 ft                     |
| Ambient Air Temperature for Storage   | -13...167 °F (-25...75 °C)       |
| Storage Relative Humidity             | 20...80 %                        |
| Storage altitude                      | 0...50000 ft (0.00...15240.00 m) |

## Ordering and shipping details

|                     |                       |
|---------------------|-----------------------|
| GTIN                | 731304329428          |
| Package weight(Lbs) | 3.62 lb(US) (1.64 kg) |

## Packing Units

|                              |                  |
|------------------------------|------------------|
| Package 1 Height             | 11.81 in (30 cm) |
| Package 1 width              | 2.76 in (7 cm)   |
| Package 1 Length             | 2.76 in (7 cm)   |
| Number of Units in Package 3 | 270              |

## Offer Sustainability

|                             |                                               |
|-----------------------------|-----------------------------------------------|
| Sustainable offer status    | Green Premium product                         |
| REACH Regulation            | <a href="#">REACH Declaration</a>             |
| EU RoHS Directive           | Compliant <a href="#">EU RoHS Declaration</a> |
| Lead free                   | Yes                                           |
| Environmental Disclosure    | <a href="#">Product Environmental Profile</a> |
| Circularity Profile         | <a href="#">End Of Life Information</a>       |
| Optimized Energy Efficiency | Energy efficient product                      |
| Take-back                   | Take-back program available                   |

## Contractual warranty

|          |                           |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|