

# Product data sheet

## Characteristics

# AP9326

## APC Leak Sensor Extension Cable - 20 ft (6.1 m)



### Overview

Presentation	Extend the length of your leak sensor to ensure proper leak detection coverage in your critical computing area.
Lead time	Usually in Stock

### Main

Number of rack unit	0U
Provided Equipment	Installation guide

### Physical

Color	Orange
Height	2.01 in (5.1 cm)
Width	9.02 in (22.9 cm)
Depth	4.80 in (12.2 cm)
Net Weight	0.71 lb(US) (0.32 kg)
Mounting preference	Lower
Mounting Mode	Not rack-mountable

### Environmental

Ambient Air Temperature for Operation	32...131 °F (0...55 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	0...95 %

### Ordering and shipping details

GTIN	731304209423
Package weight(Lbs)	0.86 lb(US) (0.39 kg)

### Packing Units

Package 1 Height	2.01 in (5.1 cm)
Package 1 width	9.21 in (23.4 cm)
Package 1 Length	6.42 in (16.3 cm)

## Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------