



Overview

Presentation	Ideal for retail, healthcare, and educational facilities, this wall mount rack offers an efficient solution for deploying server and networking equipment for edge computing applications. This rack enclosure is wall mountable, ideal for areas with limited floor space, and is designed specifically for servers and network switches, and patch panels. The cabinet's door is reversible and is compatible with APC's Netbotx security upgrade to provide remote access, video surveillance, and environmental monitoring (sold separately). Optional 120V fan tray can be top or bottom mounted (sold separately) Both the top and bottom feature knockouts of 1/2U mounting space for accessories. And several APC Smart-UPS models low-profile provide easy UPS integration and mounting. 6U Wall mount cabinet, mounting depth range of 2.87 to 20.8 inches, 200lb weight capacity, 19" rack width, ships fully assembled, ventilated with accessory integration options, 5 year APC warranty.
Lead time	Usually in Stock

Main

Number of rack unit	9U
---------------------	----

Physical

Color	Black
Height	19.09 in (48.5 cm)
Width	23.62 in (60 cm)
Depth	15.75 in (40 cm)
Net Weight	28.70 lb(US) (13.02 kg)
Mounting Support	Wall
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	12.95 in (32.89 cm)
Minimum Mounting Depth	2.87 in (7.29 cm)
Rack Width	19"
Permanent permissible load	200 lb(US) (90.72 kg) static

Conformance

Standards	UL 2416 EIA-310E
-----------	---------------------

Ordering and shipping details

GTIN	731304402688
Package weight(Lbs)	29.89 lb(US) (13.56 kg)

Packing Units

Package 1 Height	22.24 in (56.5 cm)
Package 1 width	26.97 in (68.5 cm)
Package 1 Length	19.09 in (48.5 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------