

# Product data sheet

## Characteristics

# AR112SH4

## APC NetShelter 12U Wallmount Rack Enclosure Cabinet Single Hinged Switch Depth



### Overview

#### Presentation

Ideal for retail, healthcare, and educational facilities, this wall mount rack offers an efficient solution for deploying server and networking equipment for edge computing applications. This rack enclosure is wall mountable, ideal for areas with limited floor space, and is designed specifically for servers and network switches, and patch panels. The cabinet's door is reversible and is compatible with APC's Netbox security upgrade to provide remote access, video surveillance, and environmental monitoring (sold separately). Optional 120V fan tray can be top or bottom mounted (sold separately). Both the top and bottom feature knockouts of 1/2U mounting space for accessories. And several APC Smart-UPS models low-profile provide easy UPS integration and mounting 12U Wall mount cabinet, mounting depth range of 2.87 to 12.95 inches, 200lb weight capacity, 19" rack width, ships fully assembled, ventilated with accessory integration options, 5 year APC warranty.

#### Lead time

Usually in Stock

### Main

Number of rack unit	12U
---------------------	-----

### Physical

Color	Black
Height	24.41 in (62 cm)
Width	23.62 in (60 cm)
Depth	15.75 in (40 cm)
Net Weight	32.80 lb(US) (14.88 kg)
Mounting Support	Wall
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	12.95 in (32.89 cm)
Minimum Mounting Depth	2.87 in (7.29 cm)
Rack Width	19"
Permanent permissible load	200 lb(US) (90.72 kg) static

### Conformance

Standards	UL 2416 EIA-310E
-----------	---------------------

### Ordering and shipping details

GTIN	731304402695
Package weight(Lbs)	39.71 lb(US) (18.01 kg)

### Packing Units

Package 1 Height	27.56 in (70 cm)
Package 1 width	26.97 in (68.5 cm)
Package 1 Length	19.09 in (48.5 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------