

Product data sheet

Characteristics

AR732400

NetShelter SV 42U 1060mm Deep Side Panel
Black



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Provided equipment	Brush strips Installation guide Key(S) Slam Latches
--------------------	--------------------------------------------------------------

Physical

Color	Black
Height	74.29 in (188.7 cm)
Width	27.87 in (70.8 cm)
Depth	0.69 in (1.76 cm)
Net Weight	31.48 lb(US) (14.28 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Ordering and shipping details

GTIN	731304302407
Package weight(Lbs)	43.74 lb(US) (19.84 kg)

Packing Units

Package 1 Height	78.15 in (198.5 cm)
Package 1 width	32.56 in (82.7 cm)
Package 1 Length	4.69 in (11.9 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

RoHS exemption information

Yes

Take-back

Take-back program available

Contractual warranty

Warranty

2 years repair or replace
