

Product data sheet

Characteristics

AR8125

Adjustable Shelf 250lbs 16"-24" Deep Black



Overview

Lead time	Usually in Stock
-----------	------------------



Main

Number of rack unit	1U
Provided equipment	Installation guide Mounting Hardware

Physical

Color	Black
Height	1.73 in (4.4 cm)
Width	19.49 in (49.5 cm)
Depth	17.99 in (45.7 cm)
Net Weight	12.02 lb(US) (5.45 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Rack-mounted
Maximum Mounting Depth	25.25 in (64.14 cm)
Minimum Mounting Depth	18.00 in (45.72 cm)
Rack width	19"

Ordering and shipping details

GTIN	731304282402
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	25.24 in (64.1 cm)
Package 1 Width	2.99 in (7.6 cm)
Package 1 Length	25.24 in (64.1 cm)
Package 1 Weight	16.03 lb(US) (7.27 kg)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------