

Product data sheet

Characteristics

AR8186

APC NetShelter Cable Management, Cable Ladder Attachment Kit, for Enclosures, Troughs, and Zone Cabling 4U Patch Frame



Overview

Presentation

Cable ladder attachment kit includes two adjustable brackets that can mount to a variety of surfaces providing attachment points for cable ladder systems. This flexible bracket attaches to a variety of surfaces such as top of cable troughs as a ladder elevation method, NetShelter Enclosure roofs for direct ladder routing to the enclosure, and as an attachment kit for the Overhead Zone Cabling 4U Patch Frame (VDIM33174).

Lead time

Usually in Stock

Main

Provided equipment	Installation guide Mounting Hardware 2 x Brackets
--------------------	---

Physical

Color	Black
Height	6.36 in (16.15 cm)
Width	3.41 in (8.65 cm)
Depth	2.56 in (6.5 cm)
Net Weight	0.62 lb(US) (0.28 kg)
Mounting Location	Top
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Ordering and shipping details

GTIN	731304266396
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.74 in (9.5 cm)
Package 1 Width	4.88 in (12.4 cm)
Package 1 Length	7.32 in (18.6 cm)
Package 1 Weight	1.65 lb(US) (0.75 kg)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------