

Product data sheet

Characteristics

AR8560

APC NetShelter Cable Management, Cable Trough, Open Bottom, Black, 597 x 191.4 x 316.2 mm



Overview

Presentation	Trough system to route power distribution cabling between the top of an InfraStruXure PDU to an InRow NetShelter SX Enclosure.
Lead time	Usually in Stock



Main

Number of rack unit	0U
Provided equipment	Installation guide 1 x 8 inch/20cm grounding strap

Physical

Color	Black
Height	7.54 in (19.14 cm)
Width	23.50 in (59.7 cm)
Depth	12.45 in (31.62 cm)
Net Weight	10.05 lb(US) (4.56 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Conformance

Product Certifications	UL Classified
------------------------	---------------

Ordering and shipping details

GTIN	731304259664
Package weight(Lbs)	16.20 lb(US) (7.35 kg)

Packing Units

Package 1 Height	12.40 in (31.5 cm)
Package 1 width	27.95 in (71 cm)
Package 1 Length	17.32 in (44 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------