



### Overview

|           |                  |
|-----------|------------------|
| Lead time | Usually in Stock |
|-----------|------------------|

### Main

|                    |                    |
|--------------------|--------------------|
| Provided equipment | Installation guide |
|--------------------|--------------------|

### Physical

|                     |                       |
|---------------------|-----------------------|
| Color               | Black                 |
| Height              | 0.05 in (0.12 cm)     |
| Width               | 12.36 in (31.4 cm)    |
| Depth               | 7.03 in (17.85 cm)    |
| Net Weight          | 1.17 lb(US) (0.53 kg) |
| Mounting preference | No preference         |
| Mounting Mode       | Not rack-mountable    |

### Ordering and shipping details

|                     |                       |
|---------------------|-----------------------|
| GTIN                | 731304261605          |
| Package weight(Lbs) | 3.35 lb(US) (1.52 kg) |

### Packing Units

|                  |                    |
|------------------|--------------------|
| Package 1 Height | 1.46 in (3.7 cm)   |
| Package 1 width  | 16.93 in (43 cm)   |
| Package 1 Length | 12.05 in (30.6 cm) |

### Offer Sustainability

|                            |                                                                                 |
|----------------------------|---------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                           |
| REACH Regulation           | REACH Declaration                                                               |
| REACH free of SVHC         | Yes                                                                             |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Toxic heavy metal free     | Yes                                                                             |
| Mercury free               | Yes                                                                             |
| RoHS exemption information | Yes                                                                             |
| Take-back                  | Take-back program available                                                     |

Contractual warranty

|          |                           |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|