

Product data sheet

Characteristics

AR8621

APC NetShelter Cable Management, Vertical Cable Manager, Toolless Hook and Loop Cable, Set of 10, 381 x 211 x 127 mm



Overview

Lead time	Usually in Stock
-----------	------------------



Main

Number of rack unit	0U
Provided equipment	<p>Installation guide 457mm hook and loop black cable straps 10 x 457 mm hook-and-loop strap 1 x velcro strap roll</p>

Physical

Height	0.83 in (2.11 cm)
Width	1.50 in (3.81 cm)
Depth	0.50 in (1.27 cm)
Net Weight	0.09 lb(US) (0.04 kg)
Mounting Location	Side
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Conformance

Product Certifications	TAA compliance
------------------------	----------------

Ordering and shipping details

GTIN	731304258650
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.22 in (8.18 cm)
Package 1 Width	4.66 in (11.837 cm)
Package 1 Length	7.07 in (17.95 cm)
Package 1 Weight	0.35 lb(US) (0.16 kg)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------