

Product data sheet

Characteristics

AR8725

Valueline, Vertical Cable Manager for 2 & 4 Post Racks, 84"H X 6"W, Double-Sided with Doors



Overview

Presentation

This 6" wide, high capacity vertical cable manager for 2 and 4 Post open frame racks features a double-sided cable channel with multiple internal cable tie-off locations and smooth plastic fingers at 1U increments for organized patching applications.

Lead time

Usually in Stock

Main

Provided equipment	Doors Installation guide Mounting Hardware
--------------------	--

Physical

Color	Black
Height	84.02 in (213.4 cm)
Width	5.98 in (15.2 cm)
Depth	22.52 in (57.2 cm)
Net Weight	31.06 lb(US) (14.09 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Ordering and shipping details

GTIN	731304300861
Package weight(Lbs)	37.59 lb(US) (17.05 kg)

Packing Units

Package 1 Height	12.28 in (31.2 cm)
Package 1 width	12.99 in (33 cm)
Package 1 Length	45.98 in (116.8 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information

Yes

Take-back

Take-back program available

Contractual warranty

Warranty

2 years repair or replace
