

Product data sheet

Characteristics

8910DP22V02Y181Y248

Contactor, Definite Purpose, 25A, 2 pole,
110/120 VAC 50/60 Hz coil, open, with cover,
bulk packaged

Main

Product or component type	Definite Purpose Contactor
Line Rated Current	20 A
Number of Poles	2P
Pole contact composition	2 NO
Range of product	DP
Type of packing	Bulk
Provided equipment	Terminal cover

Complementary

Maximum Horse Power Rating	2 Hp 115 V AC, 1 phase 3 hp 230 V AC, 1 phase
Locked rotor rated current	125 A 460 V AC 100 A 575 V AC 150 A 277 V AC
[Ue] rated operational voltage	600 V AC
[Uc] control circuit voltage	120 V AC 60 Hz 110 V AC 50 Hz
Phase	1 phase
Electrical connection	Quick connect terminals Binder head

Environment

Product certifications	UL Recognized CSA
------------------------	----------------------

Ordering and shipping details

Category	21354 - 8910 DP 22
Discount Schedule	CP1B
GTIN	00785901979937
Nbr. of units in pkg.	20
Package weight(Lbs)	10.5 lb(US) (4.76 kg)
Returnability	No
Country of origin	US

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------
