

Product data sheet

Characteristics

8910DPA23V02Y122Y236

CONTACTOR 600VAC 25AMP DPA

+OPTIONS

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Product or component type Definite Purpose Contactor

Line Rated Current 25 A

Number of Poles 3P

Pole contact composition 3 NO

Range of product DPA

Complementary

Motor power hp	2 hp 115 V AC 1 phase 5 hp 230 V AC 1 phase 10 hp 230 V AC 3 phases 15 hp 460 V AC 3 phases 20 hp 575 V AC 3 phases
----------------	---

Locked rotor rated current	125 A 460 V AC 100 A 575 V AC 150 A 277 V AC
----------------------------	--

System Voltage	600 V AC
----------------	----------

[Uc] control circuit voltage	110 V AC 50 Hz 120 V AC 60 Hz
------------------------------	----------------------------------

Phase	3 phases
-------	----------

Electrical connection	Pressure wire clamp Binder head
-----------------------	------------------------------------

Environment

Product certifications	CE CSA UL listed
------------------------	------------------------

Ordering and shipping details

Category	21342 - 8910 DPA 2_(25 AMP)
Discount Schedule	CP1B
GTIN	00785901467526
Nbr. of units in pkg.	1
Package weight(Lbs)	1.2
Returnability	N
Country of origin	CN

Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
---------------------------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------