

Product data sheet

Characteristics

8910DPA34V02Y122Y181Y236

CONTACTOR 600VAC 30AMP DPA + OPTIONS

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product or component type	Definite Purpose Contactor
Line Rated Current	30 A
Number of Poles	4P
Pole contact composition	4 NO
Range of product	DPA
Type of packing	Bulk

Complementary

Motor power hp	2 hp 115 V AC 1 phase 5 hp 230 V AC 1 phase 10 hp 230 V AC 3 phases 15 hp 460 V AC 3 phases 20 hp 575 V AC 3 phases
Locked rotor rated current	150 A 460 V AC 120 A 575 V AC 180 A 277 V AC
System Voltage	600 V AC
[Uc] control circuit voltage	110 V AC 50 Hz 120 V AC 60 Hz
Phase	3 phases
Electrical connection	Binder head Pressure wire clamp

Environment

Product certifications	CE CSA UL listed
------------------------	------------------------

Ordering and shipping details

Category	21343 - 8910 DPA 3_(30 AMP)
Discount Schedule	CP1B
GTIN	00785901446286
Nbr. of units in pkg.	1
Package weight(Lbs)	1.5
Returnability	N
Country of origin	CN

Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
---------------------------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------