



Main

Range of Product	EcoStruxure operator terminal Expert
Product or Component Type	License
Variant	Runtime
User Language	English Italian Chinese Spanish French German Portuguese
Format	Paper
Previous software version	V3.0

Complementary

Range Compatibility	Harmony iPC
Software Designation	EcoStruxure Operator Terminal Expert
Type of License	Single (1 seat)
Software Version	V3.1 to V3.X
Operating System	Windows 7 64 bit Windows 8.1 64 bit Windows 10 64 bit
Processor name	Intel Core i5 4th generation Intel Core i3 8th generation 8109U
Graphics card	Intel HD Graphics, 1 GB

System requirements	4 GB RAM 30 GB hard-drive space
Communication port protocol	A series Ethernet CANopen slave CS/CJ series Ethernet CS/CJ series HOST link CS/CJ/NJ series Ethernet/IP DF1 DH485 Ethernet Modbus TCP/IP Ethernet TCP/IP EtherNet/IP Ethernet/Modbus TCP FX series CPU direct FX series Ethernet FX series computer link HTTP MELSEC MPI Modbus SIO master Modbus SIO slave Modbus TCP master Modbus TCP slave PacDrive Profibus DP slave Q CPU (SIO) Q series CPU direct Q series QnU CPU Ethernet Q/QnA Series Ethernet Q/QnA series serial QnA CPU (SIO) ROC Plus Ethernet ROC Plus SIO Simatic S7 Ethernet Simatic S7 MPI direct SoMachine network TIA portal Ethernet Zelio Logic IQ-R/F series Ethernet

Ordering and shipping details

Category	22569 - MAGELIS XBT-GT (AND XBT-G)
Discount Schedule	MC2
GTIN	3606489508340
Nbr. of units in pkg.	1
Package weight(Lbs)	1.94 oz (55 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.16 in (0.4 cm)
Package 1 width	6.89 in (17.5 cm)
Package 1 Length	9.84 in (25 cm)
Unit Type of Package 2	S02
Number of Units in Package 2	16
Package 2 Weight	31.04 oz (880 g)
Package 2 Height	5.91 in (15 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)