



Main

| | |
|---------------------------|------------------------------------|
| Range of product | Harmony 9001SK |
| Product or component type | Selector switch |
| Device short name | 9001SK |
| Type of operator | Both sides to centre spring return |
| Operator profile | Black standard knob |

Complementary

| | |
|-------------------------------|------------------------|
| Bezel material | Plastic |
| Mounting diameter | 1.18 in (30 mm) |
| Net weight | 0.13 lb(US) (0.059 kg) |
| Shape of signaling unit head | Round |
| Operator position information | 3 positions |
| Contacts type and composition | Without contact block |
| Mechanical durability | 500000 cycles |
| Device presentation | Basic element |

Environment

| | |
|---------------------------------------|--|
| Protective treatment | TC |
| Ambient air temperature for storage | -40...158 °F (-40...70 °C) |
| Ambient air temperature for operation | -13...158 °F (-25...70 °C) |
| Electrical shock protection class | Class II IEC 61140 |
| IP degree of protection | IP66 IEC 60529 |
| NEMA degree of protection | NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4 NEMA 4X NEMA 6 |
| Standards | JIS C 852 EN/IEC 60947-1 CSA C22.2 No 14 EN/IEC 60947-5-1 EN/IEC 60947-5-4 JIS C 4520 UL 508 |
| Product certifications | NEMA UL 508 |
| Vibration resistance | 7 gn 2...500 Hz)IEC 60068-2-6 |
| Shock resistance | 50 gn IEC 60068-2-27 |

Ordering and shipping details

| | |
|-----------------------|----------------------|
| Category | 21429 - 9001 SK,SKY |
| Discount Schedule | CS1 |
| GTIN | 00785901791935 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.2 lb(US) (0.09 kg) |
| Returnability | No |
| Country of origin | MX |

Packing Units

| | |
|------------------|----------------------|
| Package 1 Height | 7.62 in (19.355 cm) |
| Package 1 width | 3.00 in (7.620 cm) |
| Package 1 Length | 19.35 in (49.161 cm) |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation |  REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information |  Yes |
| China RoHS Regulation |  China RoHS Declaration |
| Environmental Disclosure |  Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|