



Overview

Lead time	Usually in Stock
-----------	------------------

Physical

Height	0.55 in (1.4 cm)
Width	4.92 in (12.5 cm)
Depth	4.92 in (12.5 cm)
Net Weight	0.26 lb(US) (0.12 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Conformance

Product Certifications	C-tick CE TAA compliance VCCI Class A
Standards	FCC Part 15 class A ICES-003 UL 60950-1

Environmental

Ambient Air Temperature for Operation	32...122 °F (0...50 °C)
Operating altitude	0...10000 ft
Relative Humidity	5...95 %
Ambient Air Temperature for Storage	14...140 °F (-10...60 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	5...95 %

Ordering and shipping details

GTIN	731304286684
Package weight(Lbs)	0.35 lb(US) (0.16 kg)

Packing Units

Package 1 Height	1.65 in (4.2 cm)
Package 1 width	4.92 in (12.5 cm)
Package 1 Length	5.08 in (12.9 cm)
SCC14	10731304286681

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------