



Main

Range	TeSys
Device short name	LA1LC
Product or Component Type	Auxiliary contact

Complementary

Range compatibility	TeSys Integral contactor breaker
Mounting Location	Right side
Auxiliary contacts operation	Instantaneous
Pole contact composition	2 NO + 1 NC contactor state 1 NO tripped 1 NO tripped on short-circuit
[Ui] rated insulation voltage	690 V
[Ith] conventional free air thermal current	6 A
Connections - terminals	Screw clamp terminals 2 0.00 in ² (1.5 mm ²) Screw clamp terminals 1 0.00 in ² (2.5 mm ²)
Net Weight	0.49 lb(US) (0.22 kg)

Environment

Environmental characteristic	Standard environment
------------------------------	----------------------

Ordering and shipping details

Category	22384-STARTERS,INTEGRAL,ACCESS
Discount Schedule	I11
GTIN	3389110180121
Nbr. of units in pkg.	1
Package weight(Lbs)	10.05 oz (284.9 g)
Returnability	No
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.18 in (3 cm)
Package 1 width	4.92 in (12.5 cm)
Package 1 Length	7.09 in (18 cm)
Unit Type of Package 2	S02
Number of Units in Package 2	18
Package 2 Weight	11.87 lb(US) (5.382 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------