



Overview

Presentation	Battery cabinet that includes Lithium-ion batteries, Battery Management System (BMS), switchgear, power supply, and communication interface.
Lead time	Special Order - Call for Quoted Lead Times

Main

Battery Type	Li-Ion (Lithium Ion)
Provided Equipment	Installation guide

Physical

Color	White
Height	77.56 in (197 cm)
Width	25.59 in (65 cm)
Depth	23.11 in (58.7 cm)
Net Weight	914.92 lb(US) (415 kg)
Surface Finish	Powder coated

Output

Battery Capacity	67 Ah
------------------	-------

Conformance

Standards	UL 9540A
-----------	----------

Environmental

Ambient Air Temperature for Operation	64...82 °F (18...28 °C)
Operating altitude	0...9842.52 ft (0...3000 m)
Ambient Air Temperature for Storage	32...104 °F (0...40 °C)

Batteries & Runtime

Battery Placement	Battery Cabinet
Battery manufacturer	Samsung
Device mounting	Enclosed battery cabinet

Ordering and shipping details

GTIN	731304426165
Package weight(Lbs)	952.40 lb(US) (432 kg)

Packing Units

Package 1 Height	84.65 in (2150 mm)
Package 1 width	47.24 in (1200 mm)
Package 1 Length	31.50 in (800 mm)
Package 3 width	31.50 in (80 cm)
Package 3 Length	47.24 in (120 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Tetrabromobisphenol A, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	3 years repair or replace
----------	---------------------------