



### Overview

Presentation	Network appliances enabling remote and local access control for your NetShelter SX enclosures.
Lead time	Usually in Stock

### Main

Number of rack unit	1U
Communication Port Protocol	A-Link SNMP
Provided Equipment	Cable ties Door sensor Installation guide Lock handles Proximity Card Proximity reader Rack Mounting brackets User Manual
Product Compatibility	Rack Sensor Pod 150

### General

External Sensor Connection Type	Alarm Beacon 1 Modbus Output (RS-485) 1 Relay Output 1
APC Universal Sensors Supported	Door contact Dry Contact Humidity Smoke Fluid Spot Leak Temperature Vibration
Number of Universal Sensor Ports	6
Number of Sensor Pods Supported	6
Sensor Temperature Range	15...50 °C: +/- 1 °C 32...122 °F: +/- 1.8 °F

### Physical

Height	1.73 in (4.4 cm)
Width	17.01 in (43.2 cm)
Depth	2.32 in (5.9 cm)
Net Weight	2.80 lb(US) (1.27 kg)
Mounting preference	No preference
Mounting Mode	Rack-mounted

## Environmental

Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...149 °F (-15...65 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	0...95 %

## Ordering and shipping details

GTIN	3606481978011
------	---------------

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.63 in (19.37 cm)
Package 1 Width	20.83 in (52.9 cm)
Package 1 Length	35.59 in (90.4 cm)
Package 1 Weight	5.40 lb(US) (2.45 kg)

## Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
-------------------	--