

# Product data sheet

## Characteristics

# PDM3530L2130-1680

## APC IT Power Distribution Module 3 Pole 5 Wire 30A L21-30 1680cm



### Overview

Presentation	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
Lead time	Usually in Stock

### Main

Main Input Voltage	3 phase
Main Output Voltage	120 V
Provided Equipment	Installation guide

### Physical

Color	Black
Height	5.00 in (12.7 cm)
Width	17.52 in (44.5 cm)
Depth	15.98 in (40.6 cm)
Net Weight	9.46 lb(US) (4.29 kg)

### Input

Input Frequency	60 Hz
Acceptable Input Voltage	200...240 V
Max line current	30 A

### Output

Maximum Total Current Draw per Phase	30 A
Number of power socket outlets	1 NEMA L21-30

### Conformance

Product Certifications	UL Listed
------------------------	-----------

### Ordering and shipping details

GTIN	731304272489
Package weight(Lbs)	11.46 lb(US) (5.2 kg)

### Packing Units

Package 1 Height	5.00 in (12.7 cm)
Package 1 width	17.52 in (44.5 cm)
Package 1 Length	15.98 in (40.6 cm)

## Offer Sustainability

REACH Regulation	<input checked="" type="checkbox"/> REACH Declaration
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	<input checked="" type="checkbox"/> Yes
Environmental Disclosure	<input checked="" type="checkbox"/> Product Environmental Profile
Circularity Profile	<input checked="" type="checkbox"/> End Of Life Information
Take-back	Take-back program available