

# Product data sheet

## Characteristics

# PDW22L21-20XC

## 22' CABLE EXTENDER 5-WIRE #10 AWG, UL WITH L21-20R/P



### Overview

Lead time	Usually Ships within 2 Weeks
-----------	------------------------------

### General

Provided equipment	Installation guide
--------------------	--------------------

### Physical

Color	Black
Depth	264.02 in (670.6 cm)
Height	2.52 in (6.4 cm)
Net Weight	7.01 lb(US) (3.18 kg)
Width	2.01 in (5.1 cm)

### Input

Plug standard	NEMA L21-20P
Permissible voltage	200...240 V
Max line current	20 A
Nominal Input Voltage	3 phase

### Output

Maximum Total Current Draw per Phase	20 A
Output voltage	120 V 208 V 3 phase

### Conformance

Product certifications	UL Listed
------------------------	-----------

### Ordering and shipping details

GTIN	00731304233121
Package weight(Lbs)	7.72 lb(US) (3.5 kg)

### Packing Units

Package 1 Height	4.02 in (10.2 cm)
Package 1 width	12.01 in (30.5 cm)
Package 1 Length	17.52 in (44.5 cm)

## Offer Sustainability

---

EU RoHS Directive

Not compliant

---

## Contractual warranty

---

Warranty

2 years repair or replace

---