



Overview

Presentation	Designed for all S Type models, the SRAILKIT fits four post racks with depths ranging from 20" to 28". All necessary mounting hardware is included.
Lead time	Usually in Stock

Main

Provided Equipment	Installation guide Mounting Hardware Rack Mounting brackets Screws
--------------------	---

Physical

Color	Silver
Height	2.01 in (5.1 cm)
Width	20.98 in (53.3 cm)
Depth	3.50 in (8.9 cm)
Net Weight	3.51 lb(US) (1.59 kg)
Mounting Mode	Rack-mounted

Environmental

Ambient Air Temperature for Operation	32...158 °F (0...70 °C)
Operating altitude	0...50000 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	32...158 °F (0...70 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	0...95 %

Ordering and shipping details

GTIN	731304253051
Package weight(Lbs)	5.51 lb(US) (2.5 kg)

Packing Units

Package 1 Height	2.52 in (6.4 cm)
Package 1 width	23.27 in (59.1 cm)
Package 1 Length	4.25 in (10.8 cm)
SCC14	10731304253058
Number of Units in Package 3	105

Offer Sustainability

EU RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS
Declaration

Contractual warranty

Warranty

2 years repair or replace