

Product data sheet

Specifications



Push-to-test pilot light head, Harmony 9001K, metal, without cap, 30mm, 120V

9001KT38

Main

Range of product	Harmony 9001K
Product or component type	Head for push-to-test pilot light
Device short name	K

Complementary

Bezel material	Metal
Mounting diameter	30 mm
Cap/operator or lens colour	Without cap
Bulb base	BA 9s
Light block supply	Full voltage 120 V
Shape of screw head	Round
Light source	Incandescent bulb
Operating mode	Push-to-test
[Us] rated supply voltage	120 V
Light block supply	Full voltage or resistor
Contacts type and composition	1 C/O
Size	30 mm

Environment

Product certifications	UL listed file E42259 CCN NKCR CSA LR25490 class 3211 03 CE
NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.826 cm
Package 1 Width	5.842 cm
Package 1 Length	11.43 cm
Package 1 Weight	176.901 g



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	Ae0c4eb9-0bfb-40a4-851f-5c619fbe777d
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture

Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins